


Aufsatzbacken Kreuzversatz • Top jaws slot & tenon

SRK für ROTA NCS

SRK for ROTA NCS



Aufsatzbacken weich, SRK
Soft top jaws, SRK

Technische Daten

Technical data

Futtertype Chuck type	Bezeichnung Description	ID	Material	B B [mm]	H H [mm]	L L [mm]	S [mm]	N [mm]	b [mm]	α ₁ [mm]	Schrauben Screws	Satz Set [kg]
ROTA NCS 175/3	SRK 132	0136112	16MnCr5	25.0	30.0	60.0	10.0	8.0	22.0	3.0	M8	0.76
ROTA NCS 210/3	SRK 160	0136105	16MnCr5	40.0	60.0	76.0	16.0	10.0	25.0	4.0	M12	2.9
ROTA NCS 250/3	SRK 200	0136106	16MnCr5	40.0	60.0	94.0	16.0	12.0	30.0	8.0	M12	3.9
ROTA NCS 315/3	SRK 200	0136106	16MnCr5	40.0	60.0	94.0	16.0	12.0	30.0	8.0	M12	3.9
ROTA NCS 400/3	SRK 250	0136107	16MnCr5	50.0	80.0	117.0	20.0	16.0	40.0	12.0	M16	8.2
ROTA NCS 500/3	SRK 250	0136107	16MnCr5	50.0	80.0	117.0	20.0	16.0	40.0	12.0	M16	8.2
ROTA NCS 250/6	SRK 132	0136112	16MnCr5	25.0	30.0	60.0	10.0	8.0	22.0	3.0	M8	0.76
ROTA NCS 315/6	SRK 200	0136106	16MnCr5	40.0	60.0	94.0	16.0	12.0	30.0	8.0	M12	3.9
ROTA NCS 400/6	SRK 200	0136106	16MnCr5	40.0	60.0	94.0	16.0	12.0	30.0	8.0	M12	3.9
ROTA NCS 500/6	SRK 250	0136107	16MnCr5	50.0	80.0	117.0	20.0	16.0	40.0	12.0	M16	8.2

ⓘ Bitte bestellen Sie jeweils 2 Sätze à 3 Stück = 1 Satz für 6-Backen-Futter.

ⓘ Please order 2 sets per 3 pieces = 1 set for a 6-jaw chuck.