

WITH EVERY SET OF CLAW JAWS, RECEIVE A FREE SET OF SOFT JAWS*

FREE!





SCHUNK Claw Jaws

Improve your productivity and profit from aggressive stock removal!

- ▶ **5 times the torque than conventional soft jaws by biting into the workpiece**
- ▶ **Higher RPMs due to lighter weight**
- ▶ **Less grip force loss due to centrifugal forces**
- ▶ **Varying clamp depths with exchangeable workpiece stops**
- ▶ **Fit every make and model of chuck**



EXCEPTIONAL PRECISION FROM THE COMPETENCE LEADER!



Hard Claw Jaws

For O.D.-Clamping

With fine serration 1.5 mm x 60°

Type: SZAJ

Note: Workpiece stops to adjust the clamping depth »T« are not included in our scope of delivery and have to be ordered separately!

1.5 x 60° Serration



Chuck Size	** Clamping Range	Jaw Description	Id #	N	B	H	T	G	b	Screws	Weight (set) kg	List Price
6"	31-52mm	SZAJ 16-6	176100	12	30	47	20	M6	20	M10	1,2	361
	42-67mm	SZAJ 16-7	176101	12	30	47	20	M6	20	M10	1,0	361
	58-81mm	SZAJ 16-8	176102	12	30	47	20	M6	20	M10	1,1	361
	72-97mm	SZAJ 16-9	176103	12	35	47	20	M6	20	M10	1,1	361
	88-113mm	SZAJ 16-10	176104	12	40	47	20	M6	20	M10	1,2	361
8"	35-64mm	SZAJ 20-1	138110	14	35	53	25	M6	25	M12	1,9	409
	62-92mm	SZAJ 20-2	138112	14	35	53	25	M6	25	M12	1,6	409
	92-122mm	SZAJ 20-3	138114	14	40	53	25	M6	25	M12	1,7	409
	122-153mm	SZAJ 20-4	138116	14	40	53	25	M6	25	M12	1,6	409
	144-173mm	SZAJ 20-16	138143	14	40	53	25	M6	25	M12	1,7	412
10"	43-84mm	SZAJ 25-1	138117	16	40	58	25	M6	30	M12	1,7	455
	84-128mm	SZAJ 25-2	138119	16	40	58	25	M6	30	M12	2,3	455
	128-173mm	SZAJ 25-3	138121	16	40	58	25	M6	30	M12	2,1	455
	173-214mm	SZAJ 25-4	138123	16	40	58	25	M6	30	M12	2,3	455
12"	45-111mm	SZAJ 30-5	138131	21	50	65	25	M8	30	M16	3,8	546
	108-173mm	SZAJ 30-6	138132	21	50	65	25	M8	30	M16	4,1	546
	173-238mm	SZAJ 30-7	138133	21	50	65	25	M8	30	M16	3,4	546
	238-302mm	SZAJ 30-8	138134	21	50	65	25	M8	30	M16	4,8	546
15"	50-107mm	SZAJ 38-1	138135	22	60	85	33	M8	43	M20	10,2	895
	96-160mm	SZAJ 38-2	138136	22	60	85	33	M8	43	M20	9,0	895
	156-220mm	SZAJ 38-3	138137	22	60	85	33	M8	43	M20	7,5	895
	216-280mm	SZAJ 38-4	138138	22	60	85	33	M8	43	M20	7,5	895
	276-340mm	SZAJ 38-5	138139	22	60	85	33	M8	43	M20	8,2	895
336-400mm	SZAJ 38-6	138140	22	60	85	33	M8	43	M20	9,5	895	

1/16" x 90° Serration

Chuck Size	** Clamping Range	Jaw Description	Id #	N	B	H	T	G	b	Screws	Weight (set) kg	List Price
6"	43-61mm	SZA 16-30	122110	17	35	50	20	M5	19	M12	1,3	456
	62-82mm	SZA 16-31	122111	17	35	50	20	M5	19	M12	1,2	456
	83-103mm	SZA 16-32	122112	17	35	50	20	M5	19	M12	1,1	456
	102-122mm	SZA 16-33	122113	17	40	50	20	M5	19	M12	1,2	456
	123-143mm	SZA 16-34	122114	17	40	50	20	M5	19	M12	1,6	456
8"	32-62mm	SZA 20-14	138195	17	35	50	25	M6	22	M12	1,8	449
	60-92mm	SZA 20-15	138196	17	35	50	25	M6	22	M12	1,5	449
	88-121mm	SZA 20-16	138197	17	40	50	25	M6	22	M12	1,5	449
	117-150mm	SZA 20-17	138198	17	40	50	25	M6	22	M12	1,6	449
	148-181mm	SZA 20-18	138199	17	40	50	25	M6	22	M12	1,8	449
10"	49-93mm	SZA 25-37	138180	21	50	58	25	M8	28	M16	3,3	559
	88-138mm	SZA 25-38	138181	21	50	58	25	M8	28	M16	2,9	559
	138-182mm	SZA 25-39	138182	21	50	58	25	M8	28	M16	2,7	559
	182-229mm	SZA 25-40	138183	21	50	58	25	M8	28	M16	3,2	559
12"	54-136mm	SZA 31-10	138184	21	50	58	25	M8	28	M16	3,4	586
	113-187mm	SZA 31-11	138185	21	50	58	25	M8	28	M16	3,4	586
	178-263mm	SZA 31-13	138186	21	50	58	25	M8	28	M16	3,2	586
	242-315mm	SZA 31-13	138187	21	50	58	25	M8	28	M16	4,5	586
15"	75-157mm	SZA 40-11	138300	25,5	60	78	33	M8	35	M20	8	818
	148-248mm	SZA 40-13	138302	25,5	60	78	33	M8	35	M20	8	818
	232-317mm	SZA 40-14	138303	25,5	60	78	33	M8	35	M20	8	818
	299-388mm	SZA 40-15	138304	25,5	60	78	33	M8	35	M20	9,3	818

* Only valid for corresponding Soft Jaws, does not include Full Grip Jaws and Monoblock Jaws.

** Clamping range can vary slightly depending on chuck manufacturer's specifications. Available in many other sizes including metric tongue and groove. Valid through November 2010.



Also available in ID and bar clamping jaws.