


**Weiche Aufsatzbacken**

Mit Kreuzversatz  
Type: SRK



**Soft Top Jaws**

With tongue and groove  
Type: SRK



Stahl 16 MnCr 5,  
einsatzhärtbar  
Steel 16 MnCr 5,  
suitable for  
case hardening

BERG-FUTTERTYPE BERG CHUCK TYPE	SCHUNK-Type	Ident-Nr. Id.-No.	N	S	B	H	L	α <sub>1</sub>	b	Schrauben Screws DIN 912	Satz Set kg
GFK 2/157; GFK 3/157; KF 3/160; KFN 2/160	SRK 160	136 105	10	16	40	60	76	4	25	M 12	2.9
GFK 2/187; GFK 3/187; KF 3/200; KFN 2/200	SRK 200	136 106	12	16	40	60	94	8	30	M 12	3.9
KF 3/250; KFN 2/250; GFK 2/280; GFK 3/280	SRK 250	136 107	16	20	50	80	117	12	40	M 16	8.2