


Harte Grundbacken

Einschl. Zylinderschrauben
gehärtet und präzisionsgeschliffen
Type: GB

Hard Base Jaws

Incl. screws
hardened and precision ground
Type: GB



BERG-FUTTERTYPE BERG CHUCK TYPE	SCHUNK-Type	Ident-Nr. Id.-No.	N	S	B	H	L	b	Satz Set kg
KHNC 160; KHNC 185	GB 160	159 500	18	8	20	29.5	74	32	0.75
KHNC 200	GB 200	159 502	20	10	22	35	90	40	1.21
KHNC 250; KHNC 315	GB 250	159 503	20	12	26	40	110	40	1.95
KHNC 400	GB 400	159 505	26	12	32	46	125	54	3.05