



**Weiche Aufsatzbacken**

Mit Kreuzversatz  
Typen: SRK, 2 SRK und 2 SWKK



Type SRK



Type 2 SWKK

**Soft Top Jaws**

With tongue and groove  
Types: SRK, 2 SRK and 2 SWKK



Stahl 16 MnCr 5,  
einsatzhärtbar  
Steel 16 MnCr 5,  
suitable for  
case hardening

SCHUNK-FUTERTYPE SCHUNK CHUCK TYPE	SCHUNK-Type	Ident-Nr. Id.-No.	N	S	B	H	L	a <sub>1</sub>	b	Schrauben Screws DIN 912	Satz Set kg
TH 110-25.5	SRK 114	136 115	8	8	22	47	55.3	1	17	M 8	0.9
ROTA NCR 165 <sup>2)</sup>	SRK 132	136 112	8	10	25	30	60	3	22	M 8	0.76
HSG 110	SRK 111	136 102	10	10	22	30	53	3	17	M 8	0.6
ROTA 2B 125	2 SWKK 125	126 100	16	14	40	48	60	—	29	M 12	1.5
ROTA NCO 165 <sup>1)</sup>	SRK 160	136 105	10	16	40	60	76	4	25	M 12	2.9
ROTA 2B 160	2 SWKK 160	126 101	18	18	60	60	76	—	35	M 16	3.5
ROTA NCO 200-210	SRK 200	136 106	12	16	40	60	94	8	30	M 12	3.9
ROTA 2B 200	2 SRK 200	136 118	12	16	40	60	94	8	30	M 12	2.6
ROTA NCO 250-260	SRK 250	136 107	16	20	50	80	117	12	40	M 16	8.2
ROTA 2B 250	2 SRK 250	136 120	16	20	50	80	117	12	40	M 16	5.5
ROTA NCO 315	SRK 315	136 109	16	20	50	80	149	6	50	M 16	10.9
ROTA 2B 315	2 SRK 315	136 121	16	20	50	80	149	6	50	M 16	7.4
ROTA NCO 400	SRK 400	136 117	18	22	60	100	180	12	60	M 16	22.0
ROTA 2B 400	2 SRK 400	136 122	18	22	60	100	180	12	60	M 16	14.7

1) Bitte überprüfen Sie die Anschlussmaße  
2) Bitte bestellen Sie jeweils 2 Sätze à 3 Stück = 1 Satz für das 6-Backenfutter

1) Please check the connecting dimensions  
2) Please order 2 sets per 3 pcs. = 1 set for the 6-jaw-chuck