


Weiche Aufsatzbacken

Mit Kreuzversatz
Type: SFA



Soft Top Jaws

With tongue and groove
Type: SFA



Stahl 16 MnCr 5,
einsatzhärtbar
Steel 16 MnCr 5,
suitable for
case hardening

SCHUNK-FUTTERTYPE SCHUNK CHUCK TYPE	SCHUNK-Type	Ident-Nr. Id.-No.	N	S	B	H ₁	H ₂	L	b	l	Satz Set kg
ROTA-G 160; ROTA NCW 185; ROTA-S 160; ROTA-S plus 160; ROTA THW 165; ROTA NCR 200 ¹⁾ ; ROTA THW plus 165-185; THW 165	SFA 160	153 100	8	18	20	40	36	85	32	25	1.2
ROTA-G 200; ROTA NCW 225; ROTA NCWF 210; ROTA-S 200; ROTA-S plus 200; ROTA THW 210; ROTA THW plus 215; ROTA THWB 210; THW 210 R/F; ROTA THW vario 215	SFA 200	153 101	10	20	22	47	43	105	40	35	2.0
ROTA-G 250-315; ROTA NCW 265-315; ROTA NCWF 250-315; ROTA-S 250; ROTA-S plus 250; ROTA THW 250-315; ROTA THW plus 260-315; ROTA THWB 265; THW 250-265-R/F; THW 315-R	SFA 250	153 102	12	20	30	55.5	50.5	125	40	35	3.7
ROTA-G 400; ROTA-S 315; ROTA-S plus 315; ROTA THW 400; ROTA THWB 315; THW 315-F; THW 400-R/F	SFA 315	153 103	12	26	35	60	54	145	54	45	5.6
ROTA-G 500; ROTA-S 400-500; ROTA-S plus 400-500; ROTA THW 500-630-800; ROTA THWB 400-500; THW 500-R/F; THW 630-R	SFA 400	153 104	18	30	50	80	73	180	60	50	13.5
ROTA-G 630; ROTA-S 630-800; ROTA-S plus 630-800	SFA 630	153 106	24	40	65	118	110	260	82	70	39.6
ROTA-S 1000; ROTA-S plus 1000	SFA 1000	153 108	24	40	76	150	142	350	82	70	87.0

1) Bitte bestellen Sie jeweils 2 Sätze à 3 Stück = 1 Satz für das 6-Backenfutter

1) Please order 2 sets per 3 pcs. = 1 set for the 6-jaw-chuck



Passende Grundbacken finden Sie auf Seite 63 – 64
Suitable base jaws available on page 63 – 64