



**Harte Krallen-Stangenbacken**

Mit Kreuzversatz  
Type: SZKA-ST

**Hard Claw Jaws for Bar Clamping**

With tongue and groove  
Type: SZKA-ST



Grundbackenstellung  
Position of base jaw



Stahl 16 MnCr 5,  
einsatzgehärtet  
Steel 16 MnCr 5,  
case hardened

BERG-FUTTERTYPE BERG CHUCK TYPE	Spannbereich Clamping range	Schwingkreis Swing diameter	SCHUNK-Type	Ident.-Nr. Id.-No.	N	S	B	H	T	b	Grundbackenstellung Position of base jaw		Satz Set kg
											I	II	
Ø 160, 185													
KHNC 160	10 – 47	214	SZKA-ST 161	182 150	8	18	22	40	30	32		•	0.8
KHNC 185	26 – 62	229											
Ø 200													
KHNC 200	17 – 35	223	SZKA-ST 201	182 152	10	20	22	45	35	40		•	0.9
Ø 250													
KHNC 250	14 – 46	286	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
Ø 315													
KHNC 315	24 – 93	334	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
Ø 400													
KHNC 400	24 – 92	375	SZKA-ST 311	182 156	12	26	32	50	40	54		•	2.2