


## Weiche Blockbacken

Verzahnung und Führungsnuten induktiv gehärtet und geschliffen  
Typen: SMB und SMB-H



## Soft Monoblock Jaws

Serration and guiding slots inductive hardened and ground  
Types: SMB and SMB-H



Stahl, vergütet  
induktiv härtbar  
Steel, tempered  
inductive hardenable

FORKARDT-FUTTERTYPE FORKARDT CHUCK TYPE	SCHUNK-Type	Ident-Nr. Id.-No.	B	H	h	L	Satz Set kg
F 160; F+ 160; FNC 175; KTNC 160; KTNCV 160-175	SMB 160	163 100	20	45	24	79	1.5
	SMB-H 160	163 200	20	60	39	79	2.0
F 200; F+ 200; FNC 200; KTNC 200; KTNCV 200	SMB 200	163 101	22	60	35	94	2.6
	SMB-H 200	163 201	22	80	55	94	3.6
F 250; F+ 250; FNC 250-315; KTNC/KTNCV 250-315; UNC 250-315	SMB 250	163 102	26	70	40	115	4.4
	SMB-H 250	163 202	26	100	70	115	6.5
F 315; F+ 315; FNC 400; KTNC 360-400; KTNCV 400; UNC 400	SMB 315	163 103	32	81	46	140	7.5
	SMB-H 315	163 203	32	135	100	140	13.0
F 400; F+ 400	SMB 400	163 104	45	93	53	176	15.0
F 500 L; F+ 500 L; FNC 500-630; KTNC/KTNCV 500-630; UNC 500	SMB 500	163 105	45	130	90	176	21.6