



## Harte Krallen-Stangenbacken

Mit Kreuzversatz  
Type: SZKA-ST

## Hard Claws Jaws for Bar Clamping

With tongue and groove  
Type: SZKA-ST



Grundbackenstellung  
Position of base jaw



Stahl 16 MnCr 5,  
einsatzgehärtet  
Steel 16 MnCr 5,  
case hardened

RÖHM-FUTTERTYPE RÖHM CHUCK TYPE	Spannbereich Clamping range	Schwingkreis Swing diameter	SCHUNK-Type	Ident-Nr. Id.-No.	N	S	B	H	T	b	Grundbackenstellung Position of base jaw		Satz Set kg
											I	II	
<b>Ø 160, 175</b>													
DURO 160	10 – 43	209	SZKA-ST 161	182 150	8	18	22	40	30	32		•	0.8
DURO-NC 160	10 – 42	208											
DURO-NCE 160	10 – 48	214											
DURO-NC 175	10 – 66	239											
<b>Ø 200</b>													
DURO 200	11 – 87	275	SZKA-ST 201	182 152	10	20	22	45	35	40		•	0.9
DURO-NC 200	10 – 103	291											
DURO-NCE 200	13 – 58	246											
DURO-NCES 200 schräg/angled	10 – 93	281											
DURO-NCES 200 gerade/straight	15 – 89	267											
<b>Ø 250</b>													
DURO 250	13 – 86	326	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
DURO-NC 250	13 – 108	348											
DURO-NCE 250	13 – 68	308											
DURO-NCES 250 schräg/angled	13 – 108	348											
DURO-NCES 250 gerade/straight	13 – 86	314											
<b>Ø 315</b>													
DURO 315	14 – 102	384	SZKA-ST 311	182 156	12	26	32	50	40	54		•	2.2
DURO-NC 315	14 – 137	419											
DURO-NCE 315	28 – 122	362	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
DURO-NCES 315 schräg/angled	14 – 123	405	SZKA-ST 311	182 156	12	26	32	50	40	54		•	2.2
DURO-NCES 315 gerade/straight	13 – 114	364	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
<b>Ø 400</b>													
DURO-NCE 400	85 – 167	449	SZKA-ST 311	182 156	12	26	32	50	40	54		•	2.2
DURO-NCES 400 gerade/straight	35 – 166	449											