



Harte Krallen-Stangenbacken

Mit Kreuzversatz
Type: SZKA-ST

Hard Claw Jaws for Bar Clamping

With tongue and groove
Type: SZKA-ST



Grundbackenstellung
Position of base jaw



Stahl 16 MnCr 5,
einsatzgehärtet
Steel 16 MnCr 5,
case hardened

FORKARDT-FUTTERTYPE FORKARDT CHUCK TYPE	Spannbereich Clamping range	Schwingkreis Swing diameter	SCHUNK-Type	Ident-Nr. Id.-No.	N	S	B	H	T	b	Grundbackenstellung Position of base jaw		Satz Set kg
											I	II	
Ø 200													
F 200	22 – 52	234	SZKA-ST 201	182 152	10	20	22	45	35	40		•	0.9
F+ 200	11 – 75	263											
KTNC 200	17 – 54	241											
KTNCV 200	18 – 75	263											
FNC 200	19 – 75	263											
Ø 250													
F 250	20 – 60	300	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
F+ 250	13 – 80	320											
KTNC 250	13 – 67	307											
KTNCV 250	13 – 90	326											
FNC 250	13 – 90	330											
Ø 315													
F 315	24 – 75	358	SZKA-ST 311	182 156	12	26	32	50	40	54		•	2.2
F+ 315	14 – 102	384											
KTNC 315	13 – 91	331	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
KTNCV 315	13 – 126	366											
FNC 315	13 – 125	366											
Ø 400													
KTNC 400	15 – 138	420	SZKA-ST 311	182 156	12	26	32	50	40	54		•	2.2
KTNCV 400	37 – 192	475											
FNC 400	15 – 166	448											