



Harte Krallen-Stangenbacken

Mit Kreuzversatz
Type: SZKA-ST

Hard Claw Jaws for Bar Clamping

With tongue and groove
Type: SZKA-ST



Grundbackenstellung
Position of base jaw



Stahl 16 MnCr 5,
einsatzgehärtet
Steel 16 MnCr 5,
case hardened

SCHUNK-FUTERTYPE SCHUNK CHUCK TYPE	Spannbereich Clamping range	Schwingkreis Swing diameter	SCHUNK-Type	Ident-Nr. Id.-No.	N	S	B	H	T	b	Grundbackenstellung Position of base jaw		Satz Set kg
											I	II	
Ø 160, 165, 185													
ROTA-G 160	10 – 46	198	SZKA-ST 161	182 150	8	18	22	40	30	32		•	0.8
ROTA-S plus 160	10 – 42	208											
THW 165-R	10 – 30	177											
ROTA THW plus 165	15 – 39	190											
ROTA THW plus 185	17 – 62	212											
Ø 200, 210, 215													
ROTA-G 200	24 – 62	248	SZKA-ST 201	182 152	10	20	22	45	35	40		•	0.9
ROTA-S plus 200	14 – 52	248											
THW 210-R	18 – 52	241											
ROTA THW plus 215	11 – 83	264											
Ø 250, 260													
ROTA-G 250	15 – 82	312	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
ROTA-S plus 250	13 – 62	310											
THW 250-R	13 – 65	297											
ROTA THW plus 260	19 – 82	315											
Ø 315													
ROTA-G 315	21 – 102	359	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
ROTA-S plus 315	14 – 92	386	SZKA-ST 311	182 156	12	26	32	50	40	54		•	2.2
THW 315-R	14 – 86	335	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
ROTA THW plus 315	14 – 121	373											
Ø 400													
ROTA-G 400	34 – 122	412	SZKA-ST 311	182 156	12	26	32	50	40	54		•	2.2
THW 400-R	23 – 120	410											