


Nutensteine

Vergütet und präzisionsgeschliffen
einschließlich Zylinderschrauben, DIN 912-12.9

Type: NJ



T-Nuts

Tempered and precision ground
including screws, DIN 912-12.9

Type: NJ

FUTERTYPE HOWA CHUCK TYPE	SCHUNK-Type	Ident-Nr. Id.-No.	S _{g6}	H	h	b	Gewinde Thread	Zyl.-Schraube DIN 912 Cyl.-Screw DIN 912	Max. zul. Anzieh- drehmoment Nm Max. admissible torque Nm
HO 1 MA 4; HO 24 M 5	NJ-40	146 114	10	16.0	5.0	14	M 8	M 8 x 20	30
HO 27 M 4; HO 27 M 5	NJ-53	146 119	11	17.5	6.5	16	M 8	M 8 x 22	30
HO 1 MA 6; HO 7 MA 6; HO 15 M 6; HO 22 M 6; HO 24 M 6; HO 27 M 6; HO 37 M 6; HO 47 M 6	NJ-61	146 100	12	22.0	7.0	20	M 10	M 10 x 25	50
HO 1 MA 8; HO 2 M 8; HO 7 MA 8; HO 15 M 8; HO 23 M 8	NJ-80	146 101	14	24.5	8.5	25	M 12	M 12 x 35	70
HO 22 M 8; HO 24 M 8; HO 27 M 8; HO 37 M 8; HO 47 M 8; HO 7 MA 10; HO 15 M 10; HO 23 M 10	NJ-101	146 107	16	26.5	8.5	25	M 12	M 12 x 35	70
HO 1 MA 10; HO 2 M 10	NJ-102	146 122	16	23.0	8.0	30	M 12	M 12 x 30	70
HO 22 M 10; HO 24 M 10; HO 27 M 10; HO 37 M 10; HO 47 M 10; HO 7 MA 12; HO 15 M 12; HO 23 M 12	NJ-120	146 108	18	27.5	9.5	30	M 14	M 14 x 40	130
HO 1 MA 12; HO 2 M 12	NJ-121	146 103	18	33.5	13.5	30	M 14	M 14 x 45	130
HO 27 M 12; HO 37 M 12; HO 47 M 12	NJ-122	146 112	21	29.0	10.5	35	M 16	M 16 x 40	150
HO 1 MA 15; HO 1 M 18; HO 1 MA 21; HO 1 MA 24	NJ-154	146 128	26	40.0	17.0	50	M 20	M 20 x 50	300