


### Weiche Spanneinsätze, Type SW

für Pendelbacken

Zum Ausdrehen eines Spanndurchmessers



### Soft Clamping Inserts, Type SW

for Pendulum Jaws

For machining clamping diameters



Stahl 16 MnCr 5,  
einsatzhärtbar  
Steel 16 MnCr 5,  
suitable for  
case hardening

SCHUNK-Type	Ident-Nr. Id.-No.	Pendelbrücke Typ Pendulum Body type	B	H	L	G	Satz Set kg
SW 200-1	194 146	PB 200-1	16	15	25.5	M 6	0.15
SW 200-2	194 147	PB 200-2	20	15	25.5	M 6	0.19
SW 200-3	194 148	PB 200-3; PB 200-4	25	15	25.5	M 6	0.23
SW 250-1	194 116	PB 250-1; PB 250-2; PB 250-3	18	13	30	M 6	0.17
SW 250-2	194 117	PB 250-4; 250-5	30	15	30	M 6	0.31
SW 315-1	194 118	PB 315-1; 315-2	25	13	30	M 6	0.23
SW 315-2	194 119	PB 315-3; PB 315-4; PB 315-5	35	15	30	M 6	0.36
SW 400-1	194 120	PB 400-1	30	17	35	M 8	0.43
SW 400-2	194 121	PB 400-2; PB 400-3; PB 400-4 PB 500-4	40	19	35	M 8	0.62
SW 500-1	194 122	PB 500-5 PB 630-5	60	20	35	M 8	0.98
SW 630-1	194 123	PB 630-6	70	22	35	M 8	1.28

**Hinweis:**

Zum Ausdrehen der weichen Spanneinsätze erhalten Sie ein kostenloses Ausdrehset zum Festsetzen der Pendelbrücken.

**Note:**

For machining the soft clamping inserts, you are receiving a boring kit free of charge.