


## Nutensteine

Vergütet und präzisionsgeschliffen  
einschließlich Zylinderschrauben, DIN 912-12.9  
Type: NJ



## T-Nuts

Tempered and precision ground  
including screws, DIN 912-12.9  
Type: NJ

MMK/MATSUMOTO-FUTTERTYPE MMK/MATSUMOTO CHUCK TYPE	SCHUNK-Type	Ident-Nr. Id.-No.	S <sub>g6</sub>	H	h	b	Gewinde Thread	Zyl.-Schraube DIN 912 Cyl.-Screw DIN 912	Max. zul. Anzieh- drehmoment Nm Max. adm. tight- ening torque Nm
ZA 5-5	NJ-40	146 114	10	16	5	14	M 8	M 8 x 20	30
ZA 5-6-42 <sup>1)</sup>	NJ-60	146 104	11	20	7	20	M 8	M 8 x 25	30
YA 5-6-46; ZA 5-6-46	NJ-62	146 133	12	18.5	7.5	20	M 10	M 10 x 25	50
ZA 6-8-52; ZA 6-8-66	NJ-81	146 121	14	22	8.5	25	M 12	M 12 x 30	70
ZA 8-10-66; HA 8-10-66; ZA 6-10-75	NJ-102	146 122	16	23	8	30	M 12	M 12 x 30	70
ZA 8-12-78	NJ-125	146 139	18	25.5	9.5	30	M 14	M 14 x 40	130
ZA 11-15-120; HA 15-18-16; ZA 8-15-120	NJ-151	146 105	22	39.5	19.5	50	M 20	M 20 x 50	300

1) Bitte bestellen Sie für die Backentypen SKNL 160 und HSKN 160 getrennte Nutensteine, Ident-Nr. 10011254

1) Please order for jaw types SKNL 160 and HSKN 160 separated T-Nuts, Id.-No. 10011254