



Harte Krallen-Stangenbacken

Mit Kreuzversatz
Type: SZKA-ST

Hard Claw Jaws for Bar Clamping

With tongue and groove
Type: SZKA-ST



Grundbackenstellung
Position of base jaw



Stahl 16 MnCr 5,
einsatzgehärtet
Steel 16 MnCr 5,
case hardened

SMW/AUTOBLOK-FUTTERTYPE SMW/AUTOBLOK CHUCK TYPE	Spannbereich Clamping range	Schwingkreis Swing diameter	SCHUNK-Type	Ident-Nr. Id.-No.	N	S	B	H	T	b	Grundbackenstellung Position of base jaw		Satz Set kg
											I	II	
Ø 160, 170, 175													
HG-F 160	12 – 28	193	SZKA-ST 161	182 150	8	18	22	40	30	32		•	0.8
HG-N 160	17 – 43	191											
KNCS 175	13 – 38	186											
KNCS-N 170	17 – 44	192											
Ø 200, 210, 225													
HG-F 210	13 – 59	247	SZKA-ST 201	182 152	10	20	22	45	35	40		•	0.9
HG-N 210	17 – 62	240											
KNCS 200	18 – 58	236											
KNCS-N 210	16 – 89	267											
KNCS-N 225	16 – 81	259											
Ø 250, 260													
HG-F 260	22 – 55	295	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
HG-N 260	16 – 67	295											
KNCS 250	15 – 65	293											
KNCS-N 260	13 – 86	314											
Ø 315													
HG-F 315	18 – 86	382	SZKA-ST 311	182 156	12	26	32	50	40	54		•	2.2
HG-N 315	17 – 100	351	SZKA-ST 251	182 154	12	20	26	45	35	40		•	1.2
KNCS 315	22 – 85	335											
KNCS-N 315	23 – 102	346											
Ø 400													
HG-N 400	24 – 128	400	SZKA-ST 311	182 156	12	26	32	50	40	54		•	2.2
KNCS 400	21 – 106	388											
KNCS-N 400	35 – 122	405											